


Optronis

Make time visible

CYCLONEPLUS SERIES

CyclonePlus-25



- ✓ AUTOMATED OPTICAL INSPECTION (AOI)
- ✓ METROLOGY AND HIGH SPEED MACHINE VISION
- ✓ LASER LINE PROFILOMETRY

- 150 fps with 5 120 x 5 120 pixels
- Global shutter with low noise pixel
- CoaXPress V2.0 interface with 4 x 12.5 Gbit/s
- Flat Field Correction (FFC)
- Short Back-Focal design
- Power and trigger via CoaXPress

www.optronis.com

CyclonePlus-25 High-Speed Machine Vision Camera

Optronis

Make time visible

DESCRIPTION

The CyclonePlus-25 is a versatile high speed and high resolution camera with low noise pixels for various machine vision applications. All CyclonePlus cameras are streaming image data at up to 50 Gb/s to a CoaXPress frame grabber for real time processing. The cameras allow flexible cooling solutions and provide short back focal (BF) distances.

- 5 120 x 5 120 pixel resolution
- low noise pixel
- up to 150 fps at full resolution

PERFORMANCE (EXAMPLES, TYP., 8 BIT, 4xCXP12)

Resolution (HxV)	Frame rate	Resolution (HxV)	Frame rate
5 120 x 5 120	150 fps	5 120 x 960	780 fps
4 096 x 4 096	187 fps	5 120 x 480	1 512 fps
256 x 4	21 496 fps	5 120 x 8	19 347 fps
EMVA1288 data (v4.0 typ.)		8 bit	10 bit
Dynamic range		56 dB	60 dB
Saturation capacity		4 000 e ⁻	4 000 e ⁻
Temporal dark noise		<7 e ⁻	3.3 e ⁻
System gain		17 e ⁻ /DN	4.4 e ⁻ /DN
Signal-to-Noise Ratio		36 dB	36 dB
Dark Signal Non-Uniformity		19 e ⁻	19 e ⁻
Photo Response Non-Uniformity		1.6 %	1.5 %
Non-Linearity Error (V3.0)		0.6 %	0.5 %

SPECIFICATIONS

Sensor type	GMAX0505, Global Shutter, Grade 1
Resolution	5 120 pixel x 5 120 pixel
Frame rate (full resolution)	20 .. 150 fps
Exposure time	8 μs .. 1 / frame rate 2 μs .. 1 / frame rate UltraShort Mode
Active area / Diagonal	12.80 mm x 12.80 mm / 18.10 mm
Pixel distance	2.5 μm x 2.5 μm
A/D conversion	8/10 Bit
Quantum efficiency (sensor, typ.)	65 % @ peak
Trigger signals	Synch IN and Synch OUT, TTL level, electrically isolated
Interface	CoaXPress 2.0 Micro-BNC (HD-BNC) connectors
Interface Configurations	4 x CXP12, 2 x CXP12, 1 x CXP12, 4 x CXP6, 2 x CXP6
Power Consumption	11 W (typ.)
Power Supply	PoCXP, ext.
Temperature Ranges (to limit case temperatur to 65°C)	- operation, amb., no cooling 0 .. +25°C / 32 .. 77°F - operation, amb., with CYP-HIS 0 .. +35°C / 32 .. 95°F - operation, amb., with CYP-FAN 0 .. +45°C / 32 .. 113°F - operation, case temperature 0 .. +65°C / 32 .. 149°F
Weight	330 g w/o mount, w/o cooling
Dimensions	65 mm x 65 mm x 65.5 mm (3D model data available)

FEATURES

Exposure Modes	Timed, TriggerWidth, TriggerControlled
Trigger Activation	RisingEdge, FallingEdge, AnyEdge
Trigger Sources	External (Synch IN), CoaXPress, software
Trigger Filter and Trigger Hold-Off Time	Yes, for external trigger source
Trigger Delay	Adjustable
Flat Field Correction (FFC)	Block-based with up to 16 reference data in camera, auto calibration Column-based
Defect Pixel Correction	Yes, factory setting or customer configuration
Digital Binning Modes	Average, Sum
Digital Binning horizontal / vertical	x1, x2, x4 / x1, x2, x4
Dual ROI	Yes
Reverse X	Yes
Reverse Y	Yes
Line Skipping (Decimation)	Yes
User Global Adjustments	Offset digital / Gain analog and digital
Programmable User Output	Yes
White Balance	Yes, with auto function ROI control, manual RGB gain
Counter and timer control	Yes
Image Stamp (Counter information in frame)	Yes
Save setup to flash and load on power-on	Yes
Over Temperature Monitoring	Yes
Firmware Update	via USB (CPH6-USB) and CXP
File Access Control	Yes, up to 3 MByte user data
Test Pattern Generation	Yes

CyclonePlus-25 High-Speed Machine Vision Camera

Optronis

Make time visible


MODELS

CyclonePlus-25-M	monochrome Camera
CyclonePlus-25-C	color Camera
Scope of delivery	Camera, brief introduction

ACCESSORIES

CYP-CM	C-Mount lens adapter
CYP-FM	F-Mount lens adapter
CYP-M42-12	M42 Mount lens adapter, BF 12 mm
CYP-M58-11,58	M58 Mount lens adapter, BF 11.58 mm
CYP-HIS	Heat Sink
CYP-FAN	Cooling Fan
CPH6-PTC	Pig Tail Cable for synch
CPH6-USB	Programming Cable

SPECTRAL SENSITIVITY



FLAT FIELD CORRECTION (FFC)


The camera allows FFC in real-time to correct non-homogeneous image intensity typically caused by non-homogeneous illumination or lens vignetting. Data of up to 16 reference images are saved in the camera.

COOLING CONCEPT


Passive heat sink or active fan can be installed by customer to adapt camera to operate at required temperatures. Alternatively, camera allows to be fixed onto a customer specific heat sink.



TECHNICAL DRAWINGS CAMERA



TECHNICAL DRAWINGS ACCESSORIES



CONTACT INFORMATION

Optronis GmbH
Ludwigstr. 2, 77694 Kehl
Germany

Phone: +49 7851 91 26 - 0
info@optronis.com
www.optronis.com

The information given herein is believed to be reliable, however Optronis makes no warranties as to its accuracy or completeness. Data sheet is subject to modifications at any time. 11.25